



Manual Chamber filter press 470 – 630

KF 047
KF 063

The manual chamber filter press is closed with a single-action hydraulic cylinder. It opens by spring return. Upon request, motorized hydraulic closure can be provided.

All necessary modifications of our filter presses are considered in the planning. So that it will be your press!

Fon | +49 (0) 2646 / 9413-0
Mail | info@filox.de
Web | filox.de

Manual Chamber filter press 470 – 630



FILOX[®] – individual solutions tailored to your requirements

Hydraulic closure using an electrically driven motorized pump with a control box.

Our manual chamber filter presses are optimally suited for sludge dewatering in small industrial sewage treatment facilities, as well as for laboratories.

The drip pan can also be used as a manual slide plate, as well as in a swivel design with a hand lever.

Additional products:

- ▶ Dropping funnel
- ▶ Screw conveyor / twin-screw conveyor
- ▶ Control bars / operating platforms
- ▶ Tilting container and roll container for cake shedding
- ▶ Feeding pumps
- ▶ Special designs in container plants
- ▶ Mobile chamber filter presses
- ▶ Heating plate for filter cake drying



Chart of possible filter press sizes and design options (custom sizes on request)

Typ	Format mm	Number of chambers max.	Filtration pressure max. bar	Filter surface max. m ²	Chamber volume max. dm ³
KF 047	470 x 470	50	30	18	210
KF 063	630 x 630	60	30	38	460